



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

CL501TN
 7818103523422
 DIRECT BURIAL LUG, 4-14 CU
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 0.38
 Length (in) 1.13
 Height (in) 0.85
 Size (Hex) or Size (Bolt) 1/4
 Stud Size (in) 17/64
 Thickness 0.20
 Size (Hex) or Size (Bolt) - in 0.25
 Hole Size (in) 0.22

General

Product Description

Copper Lay-in Lug, 14-4 AWG,
 #10 Stud, Tin Plated

Conductor(s)

Copper Solid Size (Range) 14 AWG-4 AWG
 Copper Stranded (Range) 14 AWG-4 AWG

Physical

Type of Hardware Steel - Stainless
 Type of Plating Tin - Electro Plated
 Plated (Yes or No) Y
 Product Material Copper

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175