



On Line Catalog



BURNDY Catalog Number

YA29

UPC Number

7818105040555

Description

250 CU 1-HOLE LONG 1/2

Status

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.26
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.16
B Length (in)	1.62
Pad Width (in)	1.11
Strip Length	1-11/16

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/o Inspection Window, 250 kcmil, 1/2" Stud, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	250 kcmil

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	16
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Services

Hours: 8:00 AM - 5:00 PM
Monday - Friday