

**Product Number:** 25146

**Order Abbreviation:** F48T12/CW/HO

**General Description:** 60W, 48"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI



#### Product Information

Abbrev. With Packaging Info.	F48T12CWHO 30/CS 1/SKU
Actual Length (in)	46.000
Actual Length (mm)	1168.40
Average Rated Life (hr)	12000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	4050
Mean Lumens at 25C	3281
Mean Lumens at 35C	3281
Nominal Length (in)	48.000
Nominal Length (mm)	1219.20
Nominal Wattage (W)	60.00

#### Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- Average life rating at 12 hours operation per start is 18,000 hours.