



## P1484SN: One Light Pendant



**Collection:** Marino

**UPC #:**014817581355

**Finish:** Satin Nickel (SN)

### Dimensions:

<b>Diameter:</b>	9 1/4"	<b>Overall Height:</b>	62 1/8"
<b>Height:</b>	16 1/4"	<b>Wire:</b>	180" (color/Clear Silver)
<b>Weight:</b>	2.25 lbs.	<b>Mounting Proc.:</b>	Screw Collar - Stem
		<b>Connection:</b>	Mounted To Box

### Bulbs:

1 - Medium A19 60w Max. 120v - Not included

### Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Vintage lamp(s) recommended for aesthetics

### Material List:

1 Body - Steel - Satin Nickel  
1 6" Stem - Steel - Satin Nickel  
3 12" Stem - Steel - Satin Nickel

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

English (P1484)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Clear	1				14 3/4	9 1/4				

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	7/8			5		

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	P1484SN	1	014817581355	19.25	12.25	12	1.638	7.2	175	Yes
NJ Pallet		48		48	40	75.75	84.167	345.6		No
NV Pallet		48		48	40	75.75	84.167	345.6		No