



BIT,NAILEATER 1-1/4 (1.25) X 18.00(66PT)

Nail Eater Extreme

Cat No: 50309374

UPC No: 783310309376

Description

- Improved cutting edge provides 30% longer life span
- Patented new design for improved cutting and cleaner holes
- Self-feeding screw point draws bit through wood
- Unique patented design cutting angle - smoother starts, reduced cutting loads
- Made of super tough, heat-treated steel
- Cuts through nails and provides longer life
- Shorty bits - for working in tight places, yet still can go through three abutting 2 x 4s
- See Bit Extensions if more length is required

Specifications

- Bit Diameter : 1-1/4 IN (31.800 MM)
- Material : Heat Treated Steel
- Overall Length : 18.000 IN (457.200 MM)
- Shank Diameter : 7/16 IN (11.100 MM)
- Shank Type : Hexagonal
- Sub Brand : Nail Eater®
- Twist Length : 15.000 IN (381.000 MM)
- Type : Extreme
- Weight : 2.800 LB (1270.000 GM)