



S29751

40W/LED/HID/MB/5000K/100-277V/EX39
40 watt - LED HID Replacement; 5000K; Mogul extended base;
Adjustable beam angle; 100-277 volts

Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay, low bay and post top
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- Built-in surge protection - 1KV
- 5 year limited warranty

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)



S29751

Width (360°)	Width (270°)	Width (180°)
3.5"	7.7"	8.9"

Minimum Compartment Size		
Length	Width	Depth
8.27 inch	9.25 inch	9.25 inch

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29751	Hi-Pro	045923297519	100 - 277	40	50/60Hz	300W	65W

HID Equivalent	Power Factor	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches
175W	0.90	Mogul Extended	EX39	40W/LED/HID/MB/5000K/100-277V/EX39	Non-Dimmable	White	7-7/8"

MOD In Inches		Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature
3-1/2" (Open 8-7/8")		5200	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	-20C (-4F) to a maximum of +65C (+149F)
Pack	Package Type	CEC Status		RoHS Compliant	Fixture Type		UL Classification	Warranty
12/6	Box	Lawful for sale in California		Yes	Enclosed Rated		cULus - Wet Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051