



T8 Standard

F32T8/TL841/ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Bulb Shape	T8 [T8 (T8)]
Life 12-Hr Programstart [Hrs]	36000 h
Life 12-Hr Instant Start [Hrs]	30000 h
Life 3-Hr Program Start [Hrs]	30000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Initial lumen (Nom)	2850 lm
Color Designation	TL841
Design Mean Lumens	2710 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	32 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48


Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	25 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F32T8/TL841/ALTO 30PK
EAN/UPC - Product	046677281557
Order code	281550
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927869784105
Net Weight (Piece)	0.001 kg

T8 Standard

Dimensional drawing

Product
F32T8/TL841/ALTO 30PK



F32T8/841 48 ALTO ES

