



# T8 Plus

## F17T8/TL830/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

### Product data

#### General Information

Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Bulb Shape	T8 [ T8 (T8)]
Life 12-Hr Programstart [Hrs]	42000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus

#### Light Technical

Color Code	TL830 [ CCT of 3000K (830)]
Initial lumen (Nom)	1375 lm
Color Designation	TL830
Design Mean Lumens	1310 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85

#### Operating and Electrical

Power (Rated) (Nom)	17 W
---------------------	------

#### Mechanical and Housing

Cap-Base Information	Green Base
Nominal Length (Inch)	24

#### Approval and Application

Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	43 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg


#### Product Data

Order product name	F17T8/TL830/PLUS/ALTO 30PK
EAN/UPC - Product	046677280932
Order code	280933
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927850183003
Net Weight (Piece)	0.001 kg

## T8 Plus

### Dimensional drawing

Product



F17T8/830 24 ALTO Plus ES

