



S29920

2.5W CTC/LED/27K/CL/120V
2.5 watt B11 LED; Clear; Candelabra base; 2700K; 200 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 25 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures



S29920

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S29920	045923299209	120	2.5	25W	B11	Candelabra	E12

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
2.5W CTC/LED/27K/CL/120V	Dimmable	Compatible dimmers for S29920	Clear	3 7/8"	1-3/8"	200	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	80	360	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR

CEC Status	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Non-Compliant Possible sub: S9877	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051