



# S9875

4.5A19/CL/LED/E26/27K/ES/120V  
4.5 watt A19 LED; Clear; Medium base; 2700K; 450 lumens;  
120 volts

## Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures



S9875

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9875	045923098758	120	4.5	40W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
4.5A19/CL/LED/E26/27K/ES/120V	Dimmable	<a href="#">Compatible dimmers for S9875</a>	Clear	4 1/8"	2-3/8"	450	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	80	360	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR

CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Non-Compliant <a href="#">Possible sub: S8550</a>	Yes	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051