

Product 25332
Number:

Order F36T12/D/HO
Abbreviation:

General 45W, 36" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylight
Description: phosphor, 6500K color temperature, 76 CRI



Product Information

| | |
|------------------------------|-------------------------|
| Abbrev. With Packaging Info. | F36T12DHO 30/CS 1/SKU |
| Actual Length (in) | 33.909 |
| Actual Length (mm) | 861.29 |
| Average Rated Life (hr) | 9000 |
| Base | Recessed Double Contact |
| Bulb | T12 |
| Color Rendering Index (CRI) | 76 |
| Color Temperature/CCT (K) | 6500 |
| Diameter (in) | 1.593 |
| Diameter (mm) | 40.46 |
| Industry Standards | ANSI C78.81 - 2001 |
| Initial Lumens at 25C | 2500 |
| Mean Lumens at 25C | 2025 |
| Mean Lumens at 35C | 2025 |
| Nominal Length (in) | 36.000 |
| Nominal Length (mm) | 914.40 |
| Nominal Wattage (W) | 45.00 |



Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.