

Product Number: 25333

Order Abbreviation: F36T12/CW/HO

General Description: 45W, 36" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI



Product Information

Abbrev. With Packaging Info.	F36T12CWHO 30/CS 1/SKU
Actual Length (in)	33.909
Actual Length (mm)	861.29
Average Rated Life (hr)	9000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	2850
Mean Lumens at 25C	2309
Mean Lumens at 35C	2309
Nominal Length (in)	36.000
Nominal Length (mm)	914.40
Nominal Wattage (W)	45.00

Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.