

GENERATION LIGHTING

8635901EN3-71: Large One Light Outdoor Wall Lantern Dimensions:



Diameter: 9"
Width: 9"
Height: 20 7/8"
Weight: 8.2 lbs.
Extends: 10 1/4"
Wire: 6" (color/Black/White)
Mounting Proc.: Cap Nuts
Connection: Mounted To Box

Bulbs:

1 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Material List:

1 Body - Aluminum - Undefined

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990W8_3591-GRO)

Collection: Groveton

UPC #:785652055874

Finish: Antique Bronze (71)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Opal Cased Etched	1	G560247-645			16 1/8	7 1/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	18	4 3/4	7/8		9 1/2	11 1/2

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted	A19	Medium	9.3	9.3	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8635901EN3-71	1	785652055874	25	14	12	2.431	10.9	175	Yes
NJ Pallet		36		48	40	73	81.111	392.4		No
NV Pallet		30		48	40	73	81.111	392.4		No