


Product Number: 75510

Order Abbreviation: LED13T8L48DIM841SUBG8

General Description: 4ft SubstiTUBELED T8, frosted glass, 13W, Dimmable, 82CRI, 2100 Lumen, 4100K, 60000 life



Product Information

Life Time (L70)	60000
Operating Temperature (°C)	-20 to 50
Dimming	Yes
Abbrev. With Packaging Info.	LED13T8L48DIM841SUBG8 25/CS 1/SKU
Average Rated Life (hr)	60000
Base	Medium Bipin
Bulb	T8
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	4100
Color Rendering Index (CRI)	82
Lumens	2100
Approx. Lumens	2100
Nominal Voltage (V)	120.00
Nominal Wattage (W)	13.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED13T8L48DIM841SUBG8
UPC Code	UPC046135755101
Lamp Finish	Frosted