



31162-962: Nine Light Chandelier



Collection: Oslo

UPC #: 785652002960

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 26"
Height: 26 3/4"
Weight: 19.5 lbs.
Overall Height: 152 1/4"
Wire: 144" (color/Clear Silver)
Chain: 120"
Mounting Proc.: Center Lock-Up

Bulbs:

9 - Medium A19 60w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

1 Chain - Steel - Brushed Nickel
 1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1901FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Cased Opal Etched	9				5 29/32	3 15/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	13/16			5 1/2		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	31162-962	1	785652002960	27	27	15.5	6.539	24.4	250	Yes
NJ Pallet		9		48	40	75	83.333	219.6		No
NV Pallet		9		48	40	75	83.333	219.6		No