



Specification Sheet

Commercial Service[®]

G16 1/2 Globe Incandescent Lamp

Order Number **03609**

Specifications

Energy Used (Watts).....	60
Domestic Code.....	60G161/2/CB/130
Volts.....	130
Brightness (Lumens)	540
Average Rated Hours	2500
Life (in years)*	2.3
Dimmable.....	Yes
Filament Type	CC2V
Light Center Length (LCL)	1 3/4"
Estimated Yearly Energy Cost**	\$7.23
Country of Origin.....	China



Physical Characteristics

Finish	Clear
Base	Candelabra
MOL.....	2 3/4"

* Based on 3 hrs./day

* * Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee
® "Westinghouse" and "You can be sure...if it's Westinghouse" are all registered trademarks of Westinghouse Electric Corporation

