



Specification Sheet

Commercial Service[®] CA10 Flame Tip Incandescent Lamp

Order Number **03663**

Specifications

Energy Used (Watts).....	60
Domestic Code.....	60CA10/F/CB/130
Volts.....	130
Brightness (Lumens)	580
Average Rated Hours	2500
Life (in years)*	2.3
Filament Type	CC2V
Light Center Length (LCL)	1 7/8"
Estimated Yearly Energy Cost**	\$7.23
Country of Origin.....	China

Physical Characteristics

Finish	Frost
Base	Candelabra
MOL.....	4"



* Based on 3 hrs./day

* * Based on 3 hrs./day 11¢/k/Wh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
®), WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

