

SF241BS: 2 - Light Indoor Semi-Flush Mount



Dimensions:

Diameter:	15"	Height Flush:	11 1/2"
Height:	11 1/2"	Wire:	8" (color/Black/White)
Weight:	8.9 lbs.	Connection:	Mounted To Box

Bulbs:

2 - Medium A19 100w Max. 120v - Not included

Features:

•

Material List:

1 Body - Steel - Brushed Steel

Safety Listing:

Safety Listed for Dry Locations
Safety Listed for Dry Locations

Instruction Sheets:

English (SF241)

Collection: Barrington

UPC #: 014817330786

Finish: Brushed Steel (BS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Etched Glass	White Opal Etched	1				3 3/4	7				15

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy				5 1/2		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	SF241BS	1	014817330786	18	18	9	1.688	10.82	125	Yes

NJ Pallet		40		48	40	76	84.444	346.24		No
NV Pallet		40		48	40	76	84.444	346.24		No