



8535901EN3-71: Small One Light Outdoor Wall Lantern Dimensions:



Diameter:	7"	Extends:	8 1/8"
Width:	7"	Wire:	6" (color/Black/White)
Height:	16 1/8"	Mounting Proc.:	Cap Nuts
Weight:	4.7 lbs.	Connection:	Mounted To Box

Bulbs:

1 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Material List:

1 Body - Aluminum - Undefined

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990W8_3591-GRO)

Collection: Groveton

UPC #:785652055843

Finish: Antique Bronze (71)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Opal Cased Etched	1	G560246-645			12 1/4	5 1/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	14 5/8	4 3/4	7/8		7 7/8	8 1/4

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted	A19	Medium	9.3	9.3	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8535901EN3-71	1	785652055843	20.25	11.5	10	1.348	6.3	175	Yes
NJ Pallet		56		48	40	75.25	83.611	352.8		No
NV Pallet		56		48	40	75.25	83.611	352.8		No