



S9881

16.5W/LED/8"FLUSH/3K/ECO

16.5 watt; 8" Flush Mount LED Fixture; 3000K; White finish; 120 volts

Features

- Decorative flush mount LED fixture
- Easy installation
- Mounts directly to 3" and 4" junction boxes
- Edge lit
- Long life
- Excellent value



S9881

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Fixture Type	Base
S9881	BLINK™	045923098819	120	16.5	75W	Flush Mount	Connector

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
16.5W/LED/8"FLUSH/3K/ECO	Dimmable	Compatible dimmers for S9881	White	1"	8.00"	940	50000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Warm White	90	108	-17C (-2F) to a maximum of +45C (+113F)	12	Box	ENERGY STAR

CEC Status	CA Prop-65	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	MSDS
Lawful for sale in California	Warning	Yes	Yes	cETLus - Damp Location Rated	5 Year Limited	View MSDS



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051