



## SPECIFICATIONS

|                   |                          |
|-------------------|--------------------------|
| ITEM NUMBER       | F7204-30-LED             |
| DESCRIPTION       | LED CEILING/WALL FIXTURE |
| LENS              | CLEAR ACRYLIC            |
| FINISH            | WHITE - (30)             |
| MOUNTING          | CEILING / WALL           |
| CRI               | 80                       |
| CCT               | 3000K                    |
| WARRANTY          | 5 YR LIMITED             |
| SUITABLE LOCATION | DAMP                     |

## ELECTRICAL

|                 |            |
|-----------------|------------|
| LIFE HOURS      | 35,000     |
| DIMMABLE        | NO         |
| SOURCE LUMEN    | 1200       |
| DELIVERED LUMEN | 1100       |
| EFFICACY        | 104.76LM/W |
| MAXIMUM WATTAGE | 10.5W      |
| VOLTS           | 120V       |

## DIMENSIONS

|           |        |
|-----------|--------|
| HEIGHT    | 13"    |
| WIDTH     | 4-3/8" |
| EXTENSION | 3-1/4" |

## INFO

WHITE STEEL HOUSING