



8269-44: One Light Outdoor Post Lantern



Collection: Sebring

Outdoor Post Lantern Top with Weathered Copper Finish and Clear Seeded Glass.

Eye-catching style, in a weathered copper finish over solid aluminum. Clear seeded glass adds just the right sparkle. Fits 3" post (sold Separately).

UPC #:785652826948

Finish: Weathered Copper (44)

Dimensions:

Diameter: 11 1/4" **Extends:** 16"
Height: 15 3/4" **Wire:** 6 1/2"
Weight: 3.4 lbs. **Bulb Appearance:** Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included
 1 - LED Medium A19 8w Max. 120v - Not included
 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Aluminum - Weathered Copper
 1 Bracket - Aluminum - Weathered Copper
 1 Holder - Aluminum - Weathered Copper

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

English (HC-534)
 French (F-013)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Clear Seeded	1					5				

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8269-44	1	785652826948	18	14	17	2.479	6	250	Yes
NJ Pallet		32		48	40	72	80	192		No
NV Pallet		32		48	40	72	80	192		No