



Specification Sheet

G19 1/2 Globe Incandescent Lamp

Order Number **03827**

Specifications

Energy Used (Watts).....	25
Domestic Code.....	25G191/2/W
Volts.....	120
Brightness (Lumens)	160
Average Rated Hours	1500
Life (in years)*	1.4
Dimmable.....	Yes
Filament Type	C9
Light Center Length (LCL)	2 5/8"
Estimated Yearly Energy Cost**	\$3.01
Country of Origin.....	China



Physical Characteristics

Finish	White
Base	Medium
MOL.....	3 7/16"

* Based on 3 hrs./day

* * Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee

® WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

