



89193EN3-71: One Light Outdoor Wall Lantern



Collection: Hermitage

One Light LED Outdoor Wall Lantern in Antique Bronze Finish with Frosted Glass with Antique Bronze Banding

UPC #:785652045943

Finish: Antique Bronze (71)

Dimensions:

Width:	11"	Extends:	12 3/4"
Height:	19 3/4"	Wire:	6 1/2" (color/Black/White)
Weight:	8.8 lbs.	Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box

Bulbs:

1 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Material List:

1 Body - Aluminum - Undefined

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

Bilingual (English - French) (HC-919)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Frosted	1				10 3/4	8 3/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	9 5/8	5 1/2	1 3/8		7 3/4	12

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted		A19	Medium	9.5	9.5	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	89193EN3-71	1	785652045943	23.5	15	13.75	2.805	9	250	Yes
NJ Pallet		25		48	40	72.5	80.556	225		No
NV Pallet		25		48	40	72.5	80.556	225		No