



Color :  White

UPC Code : 078477900307

Country Of Origin : China

Available Colors :



Ivory



Light Almond

661F-10W

Decora SureSlide Quiet Fan Speed Control, 1.5A Fan, 60Hz, Single Pole and 3-Way - White

Leviton Decora SureSlide® Fan Speed Controls provide quiet operation while offering 3 distinct speed settings. Featuring a pre-set ON/OFF switch, this device allows the user to set the desired fan speed to operate automatically with the ON/OFF function. The fan speed control is ideal for libraries, study rooms and any area where ceiling fan noise could become distracting.

Technical Information

Product Features

Action : Standard ON/OFF

Available Colors : Ivory-I Wht-W Light Almond-T

California Title 24 : Yes

Color : White

Light : None

Load Rating : 600W Incandescent, 150W LED and CFL

Load Type : Incandescent, Dimmable LED, Dimmable CFL

Ordering Notes : White

Preset : Preset

Protection : Radio/TV Filter

Standards and Certifications : UL/CSA

Style Name : SureSlide

Switch Type : Single-Pole & 3-Way

Type : Electro-Mechanical

Voltage : 120 VAC

Wallplate : Order Separately

Warranty : 5-Year Limited

Features and Benefits

- New updated look.
- Integrated linear slide control precise 3-speed selection.
- Features a separate ON/OFF switch that preserves the selected brightness setting.
- Single pole or 3-way fan speed control when used with a 3-way switch.
- Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations.
- Quiet operation that is ideal for any areas where ceiling fan noise could become distracting
- Built-in radio/TV interference filter.
- Can be used to comply with 2016 California Title 24, Part 6 Indoor Lighting Switching Devices and Controls
- Available colors: White, Ivory and Light Almond.

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/> JOB NUMBER: <input type="text"/>	CATALOG NUMBERS: <table border="1"> <tr> <td><input type="text"/></td> <td><input type="text"/></td> </tr> <tr> <td><input type="text"/></td> <td><input type="text"/></td> </tr> </table>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
<input type="text"/>	<input type="text"/>				
<input type="text"/>	<input type="text"/>				

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts/

