



# S29650

25W/LED/13"FLUSH/30K/RD/WH  
25 watt; 13" Flush Mount LED Fixture; 3000K; Round Shape;  
White Finish; 120 volts

## Features

- Surface mount fixture
- Solid State LED lighting
- Long life
- 5 Year limited warranty
- Dimmable
- Wet location



S29650

| Item Number | Product Line | UPC          | Voltage | Watts | Incandescent Equivalent | Fixture Type | Base      |
|-------------|--------------|--------------|---------|-------|-------------------------|--------------|-----------|
| S29650      | BLINK        | 045923296505 | 120     | 25    | 100W                    | Flush Mount  | Connector |

| Lamp Code                  | Dimmable/Non-Dimmable | Suggested Dimmers                             | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours |
|----------------------------|-----------------------|-----------------------------------------------|--------|---------------|---------------|----------------|---------------------|
| 25W/LED/13"FLUSH/30K/RD/WH | Dimmable              | <a href="#">Compatible dimmers for S29650</a> | White  | 1"            | 13"           | 1700           | 50000               |

| Kelvin Temp | Color      | CRI | Beam Spread Deg | Operating Temperature                     | Pack | Package Type | ENERGY STAR |
|-------------|------------|-----|-----------------|-------------------------------------------|------|--------------|-------------|
| 3000        | Warm White | 90  | 108             | -17C (-1.4F) to a maximum of +45C (+113F) | 4    | Box          | ENERGY STAR |

| CEC Status               | CA Prop-65              | Material                   | RoHS Compliant | UL or ETL Listed | UL Classification           | Warranty                       |
|--------------------------|-------------------------|----------------------------|----------------|------------------|-----------------------------|--------------------------------|
| California T24 Qualified | <a href="#">Warning</a> | Housing: Die cast aluminum | Yes            | Yes              | cETLus - Wet Location Rated | <a href="#">5 Year Limited</a> |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051