



SPECIFICATION SHEET

Commercial Service® G25 Globe Incandescent Lamp

Item Number **04220**

Specifications

Energy Used (Watts).....	60
Domestic Code	60G25/VR/130
Volts	130
Brightness (Lumens)	530
Average Rated Hours	3500
Life (in years)*	3.1
Dimmable	Yes
Filament Type.....	C9
Estimated Yearly Energy Cost**	\$7.23
Package Type.....	Box
Country of Origin.....	China



Physical Characteristics

Finish.....	Clear
Base.....	Medium (E26)
MOL	4.38"

Vibration Resistant lamps are designed for vibration service only.

*Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

© WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.