

DATA -VOICE CABLE

Cat5e -Enhanced Category 5 UTP Outdoor
CMX UV Rated with Messenger
4 Pairs, 350MHz



CONSTRUCTION	
Conductor	- Solid, annealed Bare copper
Insulation	- Polyethylene
Messenger	- Solid galvanized steel
Jacket	- Black, low linear density Polyethylene
Ripcord	- Nylon

Features:

- Ideal for outdoor aerial applications
- Galvanized steel messenger for support
- Easily identified color-striped pairs
- 24 AWG solid copper conductors

Standards:

- Exceeds TIA/EIA-568B.2
- ETL Listed RoHS compliant
- 70°C temperature rating
- Flamability test IEC-332-1

Part #	AWG	Pairs	Nom. O.D.	Lbs./M'
J482404-01	24	4	5.40 mm x 2.60 mm"	34

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

COLOR CODE CHART

Pairs	Color
1	White/Blue Stripe & Blue/White Stripe
2	White/Orange Stripe & Orange/White Stripe
3	White/Green Stripe & Green/White Stripe
4	White/Brown Stripe & Brown/White Stripe