



S28766

11.5A19/LED/30K/ND/120V
11.5 watt; A19 LED; 3000K; Medium base; 220° beam spread; 120 volts

Features

- A-Shaped replacement lamp
- 75w equivalent
- Approved for enclosed fixtures
- Damp location rated



S28766

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S28766	045923287664	120	11.5	75W	0.95	A19	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	11.5A19/LED/30K/ND/120V	Non-Dimmable	Frosted	4-5/8"	2-3/8"	1100	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Soft White	80	220	-25C (-13F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR

CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Non-Compliant Possible sub: S8651	Yes	Yes	cULus - Damp Location Rated	3 Year Limited - 10 hour use per day



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051