



## SURECRIMP® CLND 2 HOLE LONG BARREL



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 500 kcmil - 8 AWG, #8 - # 2 SOL UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded Conductor Range with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207.
- For Bent Tang options search CLN9 or CLN4.

Conductor Size	Alternate Conductor	Expanded	Bolt/Stud Size	Mounting Hole	Mounting Hole	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog	Outside Diameter	Inside Diameter	Standard Package	Item ID	NAED/U PC
#1 AWG	#2 FLEX	1-6 AWG	1/2	1-3/4	0.5620	3.0000	0.6730	1.3750	1.4370	4.7050	GREEN	I-37	ILD-37	0.4680	0.3590	10	CLND-1-12-134	0783669 635508