



CRAM MINING LUGS



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Sight Hole.
- Color Coded.
- Maximum conductivity and excellent crimping characteristics.
- UL Listed and CSA Certified.
- Temperature Rating 90° C.
- If proper high voltage spacings and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Ease of wire insertion with flared end.
- For Copper Conductor only.
- Listed with IISCO MT-25.
- UL File E6207

Item ID	Conductor Size	Alternate Conductor Size	Bolt/Stud Size	Color Code	Tang Width	Outside Diameter	Inside Diameter	Standard Package Quantity	NAED/UPC Number
CRA-2/0-38M	2/0 FLEX	3/0 AWG	3/8	ORANGE	0.8940	0.6300	0.5120	50	0783669098334