LEG



DIMMABLE COMPACT LED DC 120V/277V MAGNETIC DRIVERS

Approximate Sizes and Weight (FOR USE WITH STANDARD OR MAGNETIC LOW VOLTAGE DIMMER)

TYPE	Input(120V)(277V)	Output	Depth	Height	Width
EUM-DC-12-40-120	1@40 Watts	12V DC	2-1/4"	5"	2"
EUM-DC-12-60-120	1@60 Watts	12V DC	2-1/2"	6"	2-1/4"
EUM-DC-12-100-120	1@100 Watts	12V DC	2-1/2"	6"	2-1/4"
EUM-DC-12-150-120	1@150 Watts	12V DC	3"	9.8"	3"
EUM-DC-12-200-120	1@200 Watts	12V DC	3"	9.8"	3"





ELV-50

DESCRIPTION:

This quiet 50W-12V electronic stepdown transformer is designed to be used with low voltage lighting systems and is protected against overload, short circuit and over heat and has a 2 year guarantee.



2-3/8"


SPECIFICATIONS:

INPUT	120V 60Hz
OUTPUT AT MAX. LOAD	11.5V 40kHz
MAXIMUM LOAD	50W
MINIMUM LOAD W/O DIMMER	10W
MINIMUM LOAD WITH DIMMER	20W
INPUT CURRENT AT MAXIMUM LOAD	0.4A
OUTPUT CURRENT AT MAXIMUM LOAD	4A
POWER FACTOR MIN.	0.95
DIMMABLE	✓
AVAILABLE COLOR:	
BLACK	

ELV-60P

DESCRIPTION:


This quiet 60W-12V plug-in electronic step-down transformer is designed to be used with low voltage lighting systems and is protected against overload, short circuit and over heat and has a 2 year guarantee.



ELV-75

DESCRIPTION:

This quiet 75W-12V electronic step-down transformer is designed to be used with low voltage lighting systems and is protected against overload, short circuit and over heat and has a 2 year guarantee.



SPECIFICATIONS:


INPUT	120V 60Hz
OUTPUT AT MAX. LOAD	11.5V 40kHz
MAXIMUM LOAD	75W
MINIMUM LOAD W/O DIMMER	10W
MINIMUM LOAD WITH DIMMER	20W
INPUT CURRENT AT MAXIMUM LOAD	0.6A
OUTPUT CURRENT AT MAXIMUM LOAD	l 6A
POWER FACTOR MIN.	0.95
DIMMABLE	✓
AVAILABLE COLOR:	•
● BLACK	

ELV-75P

DESCRIPTION:

This quiet 75W-12V plug-in electronic step-down transformer is designed to be used with low voltage lighting systems and is protected against overload, short circuit and over heat and has a 2 year guarantee.





INPUT	120V 60Hz
OUTPUT AT MAX. LOAD	11.5V 40kHz
MAXIMUM LOAD	75W
MINIMUM LOAD W/O DIMMER	20W
MINIMUM LOAD WITH DIMMER	20W
INPUT CURRENT AT MAXIMUM LOAD	0.6A
OUTPUT CURRENT AT MAXIMUM LOAD	6A
POWER FACTOR MIN.	0.95
DIMMABLE	V
AVAILABLE COLORS:	
BLACK WHITE	