

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P300106-009

Glayse

Inspired by modern architecture. Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

- Inspired by modern architecture
- Glayse features handsome details for variety of interior design styles – including mid-century modern, luxe, transitional and modern
- Popular Brushed Nickel finish
- The frameless unbounded beveled glass creates beautiful light and reflection
- Uses two 60-watt max. medium base bulbs including LED equivalent (sold separately)
- Perfect showcase for vintage style light bulbs, including Progress Lighting's P7825-01 or P7827-01
- The structure of Glayse is the focal point of the design, where form follows function
- Shop the complete Glayse collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor
- In addition to bath areas, sconces are suitable for hall & foyers to add ambient lighting.

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass/Shade: Clear Glass Beveled Panel



Width: 14-7/8"

Height: 8-3/8"

Depth: 5-1/2"

H/CTR: 5-3/8" (glass facing up)

Glass

Width: 14-7/8"

Height: 6-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Fixture can be installed with glass facing up or down</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>9.875" W., 5.875" ht., 9.875" depth</p>	<p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Two 60w max. Medium Base</p> <p>E26 base</p>	<p>cULus Damp location listed</p> <p>1 year limited warranty</p>