LED Gimbal Down Lights

Our new and improved directional LED Gimbal Down Lights, are the perfect solution for a multitude of residential and commercial applications. The adjustable LED gimbal fixtures are 80% more efficient than incandescent luminaires and they are available in multiple trim finish options to match any style of décor.



GDL-3

Features

- Energy efficient up to 80% energy savings
- · High Brightness COB LED's
- Low power consumption
- · Warm White and Neutral White color temperatures
- · Available in two standard beam angles
- · New Construction, IC and remote installations
- cETLus listed for direct contact with insulation and combustible materials
- · Easy to install, modular design
- 50,000 hour life
- 3 year limited warranty

Residential Applications

- Kitchens
- **Pantries**
- · Laundry rooms
- Bathrooms


Commercial Applications


- Lobbies
- Retail
- Hallways
- Restaurants
- · Elevators
- · Office lighting
- Stairways

Specifications


Power Consumption	9W
Input Voltage	21V DC*, 320mA constant current
Beam Angle	25/36°
Color Temperature Warm White Neutral White	3000 K 4000 K
Lumens Warm White Neutral White	650 700
Size	3.8" x 1.7"
Approvals	cETLus listed for damp locations

^{*} Each fixture requires one constant current power supply





NOTE: WH finish is stock, all other options are special order, MOQ required.



LED Gimbal Down Lights

Our new and improved directional LED Gimbal Down Lights, are the perfect solution for a mulitude of residential and commercial applications. The adjustable LED gimbal fixtures are 80% more efficient than incandescent luminaires and they are available in multiple trim finish options to match any style of décor.

DIMMABLE UL2108 Certified

GDL-4

Features

- Energy efficient up to 80% energy savings
- · High Brightness COB LED's
- · Low power consumption
- · Warm White and Neutral White color temperatures
- · Available in two standard beam angles
- · New Construction, IC and remote installations
- cETLus listed for direct contact with insulation and combustible materials
- · Easy to install, modular design
- · 50,000 hour life
- 3 year limited warranty

Residential Applications

- Kitchens
- Pantries
- · Laundry rooms
- Bathrooms


Commercial Applications


- Lobbies
- Retail
- Hallways
- Restaurants
- Elevators
- Office lighting
- Stairways

Specifications

•	
Power Consumption	12W
Input Voltage	30V DC*, 320mA constant current
Beam Angle	25/36°
Color Temperature Warm White Neutral White	3000 K 4000 K
Lumens Warm White Neutral White	870 930
Size	5.1" x 2"
Approvals	cETLus listed for damp locations

^{*} Each fixture requires one constant current power supply.





NOTE: WH finish is stock, all other options are special order, MOQ required.

