



Representative

Catalog Number: 702 1 1/4 EG
Product ID: 7TAA005270R0007
UPC Number: 61601314098
Status: Active

Strap, 14 Gauge, Size 1-1/4 Inch, Outer Diameter Size 1.660 Inches, Electro-Galvanized Steel, For Rigid or IMC Conduit, Pipe and Electrical Metal Tubing

- Square nut is captivated on the shoulder for easy one-handed tightening.
- Straps are interchangeable with 1-1/2 Inch strut, for broader application.
- Straps are shipped assembled so counting and sorting are easier.
- Pipe and conduit sizes are shown on the strap for easy identification.

North American Specifications (UNSPSC)

UNSPSC	31151901 Metal straps
IGCC	2727 Metal straps
Brand Name	Superstrut
Type	Pipe Straps, Pipe Clamps & Hangers (Series 700)
Special Features	Bolt head is combination slot and hex head for flexibility of attachment
Application	Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.
Size	1-1/4 Inches
Material	Steel

European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Surface protection	Galvanic/electrolytic zinc plated
Rotatable	N

Packaging

Outer Quantity	50
Outer Dimensions (inches)	10.2x7.2x4.4
Weight Uom	18 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com