



Representative

**Catalog Number:** 702 1 EG  
**Product ID:** 7TAA005270R0008  
**UPC Number:** 61601314056  
**Status:** Active

Strap, 14 Gauge, Size 1 Inch, Outer Diameter Size 1.315 Inches, Electro-Galvanized Steel, For Rigid or IMC Conduit, Pipe and Electrical Metal Tubing

- Square nut is captivated on the shoulder for easy one-handed tightening.
- Straps are interchangeable with 1-1/2 Inch strut, for broader application.
- Straps are shipped assembled so counting and sorting are easier.
- Pipe and conduit sizes are shown on the strap for easy identification.

**North American Specifications (UNSPSC)**

UNSPSC	31151901 Metal straps
IGCC	2727 Metal straps
Brand Name	Superstrut
Type	Pipe Straps, Pipe Clamps & Hangers (Series 700)
Special Features	Bolt head is combination slot and hex head for flexibility of attachment
Application	Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.
Size	1 Inch
Material	Steel

**European Specifications (ETIM)**

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Surface protection	Galvanic/electrolytic zinc plated
Rotatable	N

**Packaging**

Outer Quantity	100
Outer Dimensions (inches)	9.3x7.6x5.1
Weight Uom	15.5 lbs. per 100

**Documents / Support Tools**

Technical Data Sheet US	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com