



Actual



Representative

**Catalog Number:** 5260  
**Product ID:** 7TAD012220R0000  
**UPC Number:** 78621005260  
**Status:** Active

Liquidtight Conduit Fitting, 90 Degree 4 Inch, Non-Insulated Malleable Iron

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

#### Header

3D Model Available on Website

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Connectors-90 Degree
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Outer Quantity	1
Outer Dimensions (inches)	21.6x7.5x9.4
Weight Uom	2100 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321

