



Actual



Representative

Catalog Number: 5357
Product ID: 7TAD012170R0016
UPC Number: 78621005357
EAN Number: 05414363100034
Status: Active

2 Inch 90 Degree Malleable Iron Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

| | |
|-------------|---|
| UNSPSC | 39121420 Liquid tight connectors |
| IGCC | 4585 Liquid tight connectors |
| Brand Name | T&B |
| Type | Connectors-90 Degree |
| Application | Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture. |
| Standard | UL E23018, CSA |
| Size | 2 Inch |
| Material | Malleable Iron |
| Finish | Electro Zinc Plated/Chromate Coating |

European Specifications (ETIM)

| | |
|---|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 2 inch |
| Model | 90°-elbow |
| Revolving thread | N |
| Construction type | External thread |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |
| Thread connection size | Other |
| One-piece | N |
| Material housing | Other |
| Approved in combination with protective conduit CSA | Y |
| Approved in combination with protective conduit UL | Y |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 1 |
| Inner Dimensions (inches) | 6x4.5x4 |
| Outer Quantity | 5 |
| Outer Dimensions (inches) | 21.44x4.81x6.31 |
| Weight Uom | 277.5 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com