

VS16603-BS: 3 - Light Vanity Fixture

Dimensions:

| | | | |
|----------------|-----------|------------------------|----------------|
| Length: | 22 1/8" | Extends: | 5" |
| Height: | 8 5/8" | Wire: | 8" |
| Weight: | 8.98 lbs. | Mounting Proc.: | Set Screw(s) |
| | | Connection: | Mounted To Box |

Bulbs:

3 - Medium A19 100w Max. 120v - Not included

Features:

- Fixture may be mounted in the up or down position
-

Material List:

1 Body - Steel - Brushed Steel

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

English (VS16601)



Collection: Clayton

UPC #: 014817393590

Finish: Brushed Steel (BS)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|-------------------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass | White Opal Etched | 2 | | | 3 7/8 | 5 7/8 | | 2 | | | |

Backplate / Canopy Details:

| Type | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|------------|-----------------|-------|-------|----------|---------------|-----------------|
| Back Plate | 4 1/2 | 10 | | | 2 1/8 | 6 1/2 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | Frt. Class | UPS Ship |
|--------------|------------|----------|--------------|--------|-------|--------|-------|--------|------------|----------|
| Individual | VS16603-BS | 1 | 014817393590 | 24.25 | 7.25 | 12.5 | 1.272 | 12.4 | 100 | Yes |

| | | | | | | | | | | |
|-----------|--|----|--|----|----|----|--------|-------|--|----|
| NJ Pallet | | 56 | | 48 | 40 | 74 | 82.222 | 694.4 | | No |
| NV Pallet | | 56 | | 48 | 40 | 74 | 82.222 | 694.4 | | No |