

LED Vaportight Fixture

APPLICATIONS

Introducing the Mobern VW-LED Premium grade enclosed and gasketed vaportight fixture. This Energy-Saving High Performance LED Vaportight is ideal for both indoor and outdoor applications where dust and water resistance is required. Ideal for parking garages, cold storage, marinas, barns, canopies, car washes, poultry farms, agricultural applications and other areas susceptible to corrosive and wet conditions.

FEATURES & BENEFITS

- Designed for easy assembly
- Ease of Installation and Maintenance
- Visually familiar light sourcing
- Poured in place gasket seals the enclosures from most hostile environments
- Economical Mounting System can provide dramatic savings on installation labor, thus reducing costs
- Very tough diffusers resist breakage and reduce replacement and maintenance costs
- Available in 2', 4' & 8' lengths.
- Frosted lens for reducing direct glare and image of the LED
- Optional durable stainless steel mounting hardware
- No need to drill through the housing for installation
- Optional stainless steel bail for chain/cable hung installations
- Calculated Life: L70 > 54,000 hrs, 113,000 hrs calculated
- ETL listed for wet location
- Consult for other options
- Made with US Steel and plastic
- **BAA/ARRA** Compliant













Options

Location

Dimmable

Occupancy Sensor

Occupancy Sensor -

Emergency Battery Pack

Emergency Battery Pack

10W ~1300 Lumens

Internal Microwave Photocell 120V

Photocell 277V

Occupancy Sensor - Wet


Occupancy Sensor - 0-10V

SPECIFICATIONS

High quality enclosed fiberglass fixture features a unique continuous poured gasket which completely fills channel for maximum seal integrity. Diffuser is held in place with POM retaining latches. Stainless steel latches are recommended for the following applications: agriculture, car washes. food processing and swimming pools. Hole is 7/8" diameter and is provided with a plastic plug on one end for conduit attachment. Offset mounting pads which keeps luminaire level and slightly off of mounting surface are formed within the housing. Standard diffuser is high impact acrylic with textured pattern designed for high efficiency while providing reduced glare. Listed by and bears ETL label.

ORDERING DATA

EXAMPLE: VW2P-LED22DMVRF40



4W ~450 Lumens EM₅ **Emergency Battery Pack** 5W ~650 Lumens EM7 **Emergency Battery Pack** 7W ~900 Lumens

**See chart on page 2 for whip & cord ordering options

Values based on ambient temp of 25 degrees celcius and 4000K Lumens are subject to a tolerance ±10%

74

74W

Wattage is approximate and subject to a tolerance of ±5%

Dimensions and specifications subject to change without notice.











800-444-WATT → www.mobern.com → 8200 Stayton Dr., Ste. 500, Jessup, MD 20794

JOB NAME

CAT#



TYPE



**Cord & Whip Ordering Chart (Add to End of Fixture Part Number)						
Part No.	# of Wires	Length	End Fitting	Finish	Voltage	Amps (TL Only)
WP - Whip CS - Cordset	(Blank) 3 Wire 4 - 4 Wire 5 - 5 Wire 6 - 6 Wire	(Blank) 6 feet 8 - 8 feet 10 - 10 feet 12 - 12 feet 15 - 15 feet	(Blank) No Plug P* - Standard Plug TL* - Twist Lock	BK - Black WH - White	(Blank) 120-277V 120 - 120V 277 - 277V 347 - 347V 480 - 480V	15 - 15 Amps 20 - 20 Amps

ACCESSORIES

Clips and Hangers Accessories



- Replacement white latch (sold
- **H123 -** 2 Ft., 4 Ft. & 8 Ft.*



- Stainless steel latch kit set
- H126 2 Ft. & 4 Ft.
- H127 8 Ft.



- Stainless steel mounting bracket
- Mounts fixture at 45° angle from wall or ceiling
- VW-MB2L-2PK-45DEG



- Stainless steel mounting bracket w/bail
- VW-MB2L-B-2PK
- (Recommended for cable hanging)




- Stainless steel mounting bracket
- ♦ VW-MB2L-2PK

Note:

To replace latches on entire fixture order 6 latches for 2 Ft., 8 latches for 4 Ft., and 14 latches for 8 Ft.


DIMENSIONS

Side View



Size	ize Operating Temperature Range			
2 ft	- 20°C (-4°F) to 39°C (102°F)			
4 ft	- 20°C (-4°F) to 35°C (95°F)			
8 ft	- 20°C (-4°F) to 39°C (102°F)			

End View



Values based on ambient temp of 25 degrees celcius and 4000K Lumens are subject to a tolerance ±10%

Wattage is approximate and subject to a tolerance of ±5% Dimensions and specifications subject to change without notice.











800-444-WATT → www.mobern.com → 8200 Stayton Dr., Ste. 500, Jessup, MD 20794

CAT# JOB NAME

