



S8550

5A15/CL/LED/E26/27K/90CRI/120V
5 watt A15 LED; Clear; Medium base; 2700K; 500 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures



S8550

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S8550	045923085505	120	5	40W	A15	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
5A15/CL/LED/E26/27K/90CRI/120V	Dimmable	Compatible dimmers for S8550	Clear	3-3/8"	1-7/8"	500	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	90+	360	-20C (-4F) to a maximum of +45C (+113F)	12/1	CD/1	ENERGY STAR
CEC Status	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty		
Lawful for sale in California	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	3 Year Limited		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051