



Hoffman

Screw-Cover, Type 3R

Catalog Number: A18R188NK
US List Price (USD): \$163.00

Bulletin Number:

- A90S3

Finish:

- ANSI 61

Material:

- Steel



Model Code:

- 13516

Ship Wt. Std. Pkg. (lbs):

- 25.0

Interchangeable:

- False

Finish:

- Galv/paint

Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27525 cUL Listed per CSA C22.2 No 94;
Type 3R; File No. E27525 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Application:

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Features:

- Drip shield top and seam-free sides, front and back
- Slip-on removable cover fastened with plated steel screws along bottom edge
- Handles on larger sizes (see table)
- Embossed mounting holes on back of enclosure
- Knockouts in bottom of 16 and 14 gauge enclosures
- Provision for padlocking
- No gasketing

Specifications:

16, 14 or 12 gauge galvanized steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.

Accessories:

- Industrial Corrosion Inhibitors
- Electric Heater
- Grounding Device
- Mounting Bracket Kit
- Touch-Up Paint

Technical Data

Screw-Cover, Type 3R


Catalog Number	A18R188NK
A in.	18
B in.	18
C in.	8
D in.	—
Mounting H in.	13.00
Body Style	B
Mounting J in.	1.12

Certifications

 EU Certification

 UL Certification








Documents

 Spec Sheet

 3D STEP CAD

 Dimension Drawing

Accessories

Item			
	Mounting Bracket Kit	AMFK3RL014	
	Grounding Device	AGS816	
	Grounding Device	AGLK2	
	Grounding Device	AGS408	
	Grounding Device	AGS416	
	Grounding Device	AGS808	
	Touch-Up Paint	ATPPY61	