



BURNDY Catalog Number
UPC Number
Description
Status

YAZ6C2N
7818102085333
6STR CU-LONG-OPEN-2 NEMA
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle
Strip Length
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in

Straight
1-3/16
4.40
Skived
0.52
Long
0.12
1.12
0.83
1.75

General

Number of Holes
Product Description

2
Cu Tubing Hylug, 2 Holes with
Inspection Window, #6 AWG
Code, 600V-35kV, 1/2" stud, Long
, Compression, 0.56 in BCD , Blue

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

N/A
N/A
6 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/2
Blue
Y
7,374
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175