



S3168

75T4/CL
75 watt; Halogen; T4; Clear; 2000 Average rated Hours; 750 Lumens; Bi Pin GY6.35 base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S3168

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S3168	045923031687	75	120	T4	Bi-Pin GY6.35	GY6.35	75T4/CL

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	2-3/8"	0.50"	CC-2V	750	2900	Warm White	2000

Pack	Package Type	Dimmable/Non-Dimmable	RoHS Compliant
960/48	Box	Dimmable	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

