



S29597

9.5A19/LED/50K/ND/120V/4PK
 9.5 watt; A19 LED; Frosted; 5000K; Medium base; 220' beam spread; 120 volts; Non-Dimmable; 4-Pack

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Approved for enclosed fixtures
- Non-Dimmable



S29597

Item Number	UPC	Input Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S29597	045923295973	120	9.5	60W	A19	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9.5A19/LED/50K/ND/120V/4PK	Non-Dimmable	Frost	4-3/8"	2-3/8"	800	15000	5000
Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR	CEC Status
Natural Light	80	220	-25C (-13F) to a maximum of +45C (+113F)	12-4pks	4Pk	ENERGY STAR	Non-Compliant Possible sub: S8563
RoHS Compliant		Fixture Type		Warranty			
Yes		Enclosed Rated		3 Year Limited - 10 hour use per day			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

