




SURECRIMP® CSWS 1 HOLE SHORT W/SIGHT



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Standard barrel length with chamfered entry.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified.
- 500 kcmil - 8 AWG, #8 - # 2 SOL UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations:
- Copper - Class B concentric, Class B compressed, Class C concentric.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207.
- For Bent Tangs change the 4th letter to a B and add -4 for 45 deg. or -9 for 90 deg.

Item ID	Figure Number	Conductor Size	Alternate Conductor	Expanded	Bolt/Stud Size	Mounting Hole	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog	Outside Diameter	Inside Diameter	Standard Package	NAED/U PC
CSWS-8-14	2	#8 AWG	#8 FLEX, 8 SOL		1/4	0.2810	0.6800	0.3740	0.5000	0.5620	1.3750	RED	I-21	ILD-21	0.2720	0.1790	50	0783669 627619