

Project:

Type:

Prepared By:

Date:



UPC: 19813748719



### Features and Benefits

PREMIUM, FULL GLASS DESIGN - Mimics traditional bulbs

90 CRI - Produces rich and vibrant colors.

15,000-HOUR LIFESPAN - Lasts up to 13.7 years at 3 hours per day

ENCLOSED FIXTURE RATED - May be used in both enclosed and open fixtures

OMNIDIRECTIONAL Light output

DAMP RATED - Suitable for damp locations

### Technical Specifications

Product Type	Decorative
Bulb Shape	G25
Finish	Clear
Wattage	3W
Wattage Equivalency	40W Incandescent
Typical Lumen Output	350
Efficacy	88 lm/W
Color Temperature	2700K Soft White
CRI	90
Base Type	E26
L70 Lifespan	15,000 hours
Operating Temperature	-20°C - 45°C
Dimmable	Yes, down to 10%
Beam Angle	360°
Warranty	3-Year, No-Compromise Warranty
For Use in Emergency Fixtures	No
For Use Outdoors in Open Fixtures	No


### Electrical Characteristics

Input Voltage	120V
Power Factor	0.7
Flicker	<30%

### Listings

ETL Qualified	Yes
ENERGY STAR V2.0	This product is ENERGY STAR® Version 2.0 Certified
Energy Star ID	2330367
CEC Status	Lawful for sale in California

## Light Distribution



## Case and Pallet Dimensions

	QTY	LENGTH	WIDTH	HEIGHT
CASE	6	10.4	7	5.7
PALLET	528	42.5	38.5	39.5

## Dimension

