

# Economy 6" Super Thin Recessed LED 14W Soft White

## Type IC, Wet & Air-Tight

A Comment of the Comm	

Project:		
Location:		
Trim Finish:	Qty:	
Notes:		

## **DESCRIPTION**

Recessed 6" Round LED With Integral Driver In Connection Box. Fits Where No Other Recessed Fixture Can.

#### **FEATURES & BENEFITS**

1/2" Thin - Install Directly Under Joists, Maximum Layout Flexibility

Type IC Rated - No Housing Required
Fast & Easy To Install - Save On Labour

Driver Inside Connection Box - No Junction Box Needed


#### MOUNTING

Cut Hole In Ceiling And Snap Fixture In Opening With Attached Spring Clips. 1 1/2" Above Ceiling Clearance Required For Driver.

### DIMENSIONS

ID 6 1/8" OD 6 3/4" Cut Out 6 1/4" to 6 1/2"

SPECIFICATION						
Applications	Recessed Ceiling, Showers & Soffits					
Energy Used	14 W					
Colour Temperature	3000 K					
Light Output	900 lm					
Halogen Equivalent	75 W					
Beam Angle	110°					
CRI	80 +					
Driver Input	120V AC or 277V-347V AC					
Power Factor	0.98					
Dimming	TRIAC Dimmers 5% - 100%					
Approved Location	Insulated Ceiling & Wet IP54					
Air Tight	Yes					
Ambient Temperature	-40°F (-40°C) to +104°F (+40°C)					
Projected Life	70% Light Output at 36,000 Hours					
Certification	c <b>UL</b> us, Energy Star					
Warranty	5 Year					





## COMPLIANCE









1 4	Warehouses									
Lotus LED Lights	Vancouver	Toronto	Las Vegas	Naples	Philadelphia	Dallas	Seattle	Chicago	Denver	
Ligitis	tel: <b>1</b>	tel: <b>1-844-24-LOTUS (56887)</b>		fax. 1-877-561-6306			www.lotusLEDlights.com			

#### **CHARACTERISTICS**

Body: Durable, Die Cast Aluminum Alloy for Optimal Heat Dissipation.

Paint: Oil Based Spray Painted - Scratch Resistant And Smooth Finish.

LEDs: 48 Pieces Of 2835.

Driver: In-house produced, Triac dimmable down to 5%.


Connection Box: Saves Contractors Labour On Installation.


Quick connectors included.



#### PHOTOMETRIC DATA

LB6R 30K LAMP FLUX: 902.1 LM MODEL: VOLTAGE: 120 V LUMENS / POWER: 63.95 LM/W POWER: 14.1 W CENTRAL INTENSITY: 345 CD PF: 0.986 **BEAM ANGLE:** 109 DEGREES





ORDERING GUIDE Model: LB6R / 30K / WH

LB6R / 30K /

Trim Finish

WH: White BK: Black

Order 277V - 347V Optional Driver Separately As cat # LLL-LD1535HB **ACCESSORIES** Sold Separately

Low Volage Extension Cables 10ft - cat # EXC10, max 40ft extension

FT4 / CM rated

Flanged Rough-In Plates - cat # LRP6

Flat Rough-In Plates - cat # RIP6

Goof Ring White OD 7 5/8" - cat # GR6



Warehouses

Toronto Las Vegas **Naples** Philadelphia **Dallas** Seattle Vancouver Chicago Denver

tel: 1-844-24-LOTUS (56887)

fax. 1-877-561-6306

www.lotusLEDlights.com