



Representative Image

Catalog No. TQC100S

Description: ENCLOSURE NEMA 1 SURFACE 100A

UPC No 783164020137

Home > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Frame notes and/or restrictions:THQC, THHQC, TXQC (1, 2, 3 Pole).

Enclosure notes and/or limitation: Enclosure cannot accommodate a 3-pole breaker with accessory.

ACCESSORIES:

Neutral Kit (non-GF applications):included

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA Type 1
Mounting	Surface
Frame Type	Q-Line
Amperage	100 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5651SH1
GSA Compliance	No

Dimensions

Height	15.2 in
Depth	4.0 in
Width	6.9 in
Weight	7.4 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 1 enclosure, 100 amp max. Product Numbers TQC100F and TQC100S. 1 page outline drawing in .pdf format.	139C5651-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.