



Powering Business Worldwide

pe.eaton.com

Eaton Arrow Hart Color Coded Locking Connector

AHCL520C

UPC:032664755798

Dimensions:

- **Height:** 3.71 IN
- **Length:** 2.23 IN
- **Width:** 2.1 IN

Weight: .49 LB

Warranties: No Data

Specifications:

- **Special Features:** Voltage Color Coding
- **Type:** Locking Connector
- **Allowable Wire Size:** #14-8 AWG
- **Amperage Rating:** 20A
- **Application:** Industrial
- **Voltage Rating:** 125V
- **Wiring Method:** Back
- **Color:** Yellow, Black
- **Design Type:** Ultra grip
- **Face/Body Material:** Nylon
- **Nema Configuration:** L5-20
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Cord Diameter:** 0.38 - 1.00" (9.5 - 25.4mm)
- **Operating Temperature:** -40°C (w/o impact) to 60°C (-40°F to 140°F)

Supporting documents:

- [ah-color-coded-L5-20-locking-devices-spec-sheet.pdf](#)

Certifications:

- cULus Listed
- NOM



Product compliance:

- RoHS Compliant
- NAFTA

© 2016 Eaton. All rights reserved.